



MOLLA IN ELASTOMERO EFFBE FORATA

DRILLED EFFBE ELASTOMER SPRING


ELASTOMER-FEDER EFFBE, GELOCHT

EMP-2

Specifiche: Barre forate - EFFBE - Urelast 90 SHORE A.
Impiegate per realizzare molle in lunghezze speciali,
rondelle ammortizzanti, particolari a disegno e prototipi

Specification: Round tube stock – EFFBE – Urelast 90 SHORE A.
Used for making special length springs, conical washers, design parts and prototypes

Spezifikationen: Gelochte Stäbe - EFFBE - Urelast 90 SHORE A.
Für Federn mit Speziallängen, Dämpferscheiben, Teile nach Zeichnung und Prototypen



D	D1	L
16	6,5	300
20	8,5	300
25	10,5	300
32	13,5	300
40	13,5	300

D	D1	L
50	17	400
63	17	400
80	21	400
100	21	300
125	27	300

Esempio di ordinativo: D **Order example:** D **Bestellbeispiel:** D